

This document is valid for the following devices:


Device-No.	Designation	Series
1000022	Cremesso Compact automatic rusty red	all

1000-020-01



Pos	Item-No.	Designation	Spec.	Comment
1	6000370	HOUSING LEFT rusty-red		
139	6000520	STEEL CLAMP 9.5mm		
139	6000187	STEEL CLAMP 10mm		
2	6000376	HOUSING RIGHT rusty-red		
61	6000108	O-RING ID3.5x2.0MM		
80	6000230	FIXED LOCK		
C	6000326	DISPENSER SUB-ASSY(RAL8022/spray PU oil)		
D	6000222	WATER TANK SUB-ASSY		
J	6000295	Silicon Fiber Tube for Infusion Group		
K	6000296	Silicon Fiber Tube for S2 Sub-Assy		
W01	6000335	GS POWER CORD SUB-ASSY		


Heater



Pos	Item-No.	Designation	Spec.	Comment
E05	6000030	THERMOFUSE type G4-A00 152C		
H2	6000004	HEATING CHAMBER SET SUB ASSY		
NTC	6000037	NTC:IN-A100K-3P 100K ohm, lead wire:350m		


Brew-Unit

1000-021-03




Pos	Item-No.	Designation	Spec.	Comment
126	6000229	NOZZLE (BLACK)		
34	6000327	METAL HANDLE with titanium chrome		
42	6000337	E-RING 6x12x0.8mm type:2012-1		
44	6000336	TAPPING SCREW D3.5x10mm B/T		
N	6000301	INFUSION GROUP CYLINDER SUB-ASSY		
SW	6000033	Micro Switch Cord SUB-ASSY		

Injector-Unit




Pos	Item-No.	Designation	Spec.	Comment
133	6000103	SCREW D3.0x10mm		
44	6000336	TAPPING SCREW D3.5x10mm B/T		
47	6000199	CAPSULE HOLDER LEFT COMPLETE		
48	6000102	Spring F0.8xID9.4xL14.8		
49	6000133	CAPSULE HOLDER LEFT BLACK		
50	6000162	Capsule Lock black		
57	6000134	CAPSULE HOLDER RIGHT BLACK		
58	6000200	CAPSULE HOLDER RIGHT COMPLETE		
ML	6000293	CAPSULE HOLDER LEFT COMPLETE		
MR	6000294	CAPSULE HOLDER RIGHT COMPLETE		

Injector




Pos	Item-No.	Designation	Spec.	Comment
146	6000492	HITEC O-Ring 16x2mm for Cremesso-System.		
147	6000489	Lip Seal EPDM 70.10-07 System-Part		
53	6000094	SPRING PISTON ID8MM		
54	6000164	Piston Valve red		
DA1	6000306	Cremesso Piston Sub-Assy		

Pump



Pos	Item-No.	Designation	Spec.	Comment
156	6000274	SPRING Ø1.2xOD25/15.5xH20		
76	6000275	NEW PUMP BRACKET BLACK		
77	6000173	Rubber coupling		
78	6000171	RUBBER PUMP-SUPPORT		
79	6000147	VIBRATION PUMP 230V 50HZ ULKA EP4GW 94V0		
E10	6000031	Thermostat Terminal wire sets	Dwg# 775	
S2	6000217	VALVE S2 V2		


Main Board



Pos	Item-No.	Designation	Spec.	Comment
101	6000493	MAIN BROAD SMD-776F-MG-22000 REV-C		
125	6000175	RUBBER FOOT B D6.5x10.5mm		
32	6000338	Screw PT 3.5x12mm INOX	BN13579 KA35x12	
93	6000169	IN-OUT RUBBER RING		
95	6000234	IN-OUT VALVE		
96	6000174	RUBBER FOOT D6.0xD4x18mm		
FM	6000115	FLOWMETER 974-9501		
SW1	6000039	Rocker switch SR-08A 16(4)A/250V no indi		



Nozzle

1000-020-08



Pos	Item-No.	Designation	Spec.	Comment
106	6000132	Nozzle black V2		
107	6000086	Nozzle Cover titanium chrome		
31	6000172	Cushion		



Clean Button



Pos	Item-No.	Designation	Spec.	Comment
119	6000101	Spring F0.4xL14		
24	6000137	Button Left brown black / with silver		
26	6000135	Button Bracket Left with white		
28	6000023	CLEAN BOARD SUB-ASSY		



Coffee Button

1000-020-10



Pos	Item-No.	Designation	Spec.	Comment
119	6000101	Spring F0.4xL14		
25	6000138	Button Right brown black / with silver		
27	6000136	Button Bracket Right with white		
29	6000024	COFFEE BOARD SUB-ASSY		

Capsule Holder




Pos	Item-No.	Designation	Spec.	Comment
65	6000354	CAPSULE TRAY RAL8022 SPRAY PU OIL		
66	6000352	DISPENSER GRATE 1.0MM THK. STAINLESS		
69A	6000360	CAPSULE DISPENSER SMALL ASS. RAL8022-SIL		
70	6000353	CAPSULE DISPENSER BIG ABS RAL8022		

Water Tank

1000-020-12



71




72A



Pos	Item-No.	Designation	Spec.	Comment
71	6000357	WATER TANK-COVER TRANSPARENT-GREY		
72A	6000358	WATER TANK SUB-ASSY TRANSPARENT-GREY		
73	411445	WATER TANK VALVE-SEAL		
74	411446	SPRING OD 11.8		
75	411447	WATER TANK VALVE-BODY		

Infusion group cylinder with filter plate



Pos	Item-No.	Designation	Spec.	Comment
154	6000374	Cup head screw D3x8		